










































接线端子 弹簧连接

 - 标准型 - 双电路型  DIN 3							 双层
型号		D 2.5 / 5.2L	D 2.5 / 5.3L	D 2.5 / 5.4L	D 4 / 6.2L	D 6 / 8.2L	D 2.5 / 5.D2.L
厚度 (mm)		5	5	5	6	8	5
最大线径 (mm ²)		2.5	2.5	2.5	4	6	2.5
标准型 	型号	D 2.5 / 5.2L	D 2.5 / 5.3L	D 2.5 / 5.4L	D 4 / 6.2L	D 6 / 8.2L	D 2.5 / 5.D2.L
	订货号	1SNA 290 021 R2700	1SNA 290 031 R2100	1SNA 290 011 R2500	1SNA 290 061 R0700	1SNA 290 081 R2400	1SNA 290 161 R0000
零线型 	型号	D 2.5 / 5.N.2L	D 2.5 / 5.N.3L	D 2.5 / 5.N.4L	D 4 / 6.N.2L	D 6 / 8.N.2L	D 2.5 / 5.D2.N.L
	订货号	1SNA 290 023 R2100	1SNA 290 033 R2300	1SNA 290 013 R2700	1SNA 290 063 R0100	1SNA 290 083 R2600	1SNA 290 163 R0200
接地型 	型号	D 2.5 / 5.P.2L	D 2.5 / 5.P.3L	D 2.5 / 5.P.4L	D 4 / 6.P.2L	DB 6 / 8.P.2L	-
	订货号	1SNA 290 029 R0700	1SNA 290 039 R0100	1SNA 290 019 R0500	1SNA 290 069 R1700	1SNA 290 089 R0400	-
端板 	型号	FED5.2L	FED5.3L	FED5.4L	FED5.2L	FED8.2L	FED5.D.L
	订货号	1SNA 291 061 R2400	1SNA 291 051 R2200	1SNA 291 041 R2000	1SNA 291 061 R2400	1SNA 291 161 R2500	1SNA 291 441 R2600
电流隔板 	型号	SCD5.2L	SCD5.3L	SCD5.4L	SCD5.2L	-	
	订货号	1SNA 291 352 R0400	1SNA 291 362 R0600	1SNA 291 372 R0000	1SNA 291 352 R0400	-	
测试插头  2mm	型号	FC2					
	订货号	1SNA 007 865 R2600					
短路条  2 - 10路	型号	BJDL 5.2 至 BJDL 5.10			1) BJD L 6.2 2) BJD L 6.3 3) BJD L 6.4 4) BJD L 6.5	1) BJD L 8.2 2) BJD L 8.3 3) BJD L 8.4 4) BJD L 8.5	BJDL 5.2 至 BJDL 5.10
	订货号	1SNA 291 102 R2300 (2P) 至 1SNA 291 110 R2600 (10P)			1)1SNA 291 128 R2400(2P) 2)1SNA 291 129 R2500(3P) 3)1SNA 291 194 R1700(4P) 4)1SNA 291 195 R1000(5P)	1)1SNA 291 122 R1600(2P) 2)1SNA 291 123 R1700(3P) 3)1SNA 291 144 R2400(4P) 4)1SNA 291 145 R2500(5P)	1SNA 291 102 R2300(2P) 至 1SNA 291 110 R2600(10P)
短路条  用于两个不同厚度的端子之间	型号	BJDPL56 BJDPL58			BJDPL56 BJDPL68	BJDPL58 BJDPL68	-
	订货号	1SNA 291 150 R0600 (5/6) 1SNA 291 160 R0000 (6/8)			1SNA 291 150 R0600(5/6) 1SNA 291 170 R0200(6/8)	1SNA 291 160 R0000(5/8) 1SNA 291 170 R0200(6/8)	-
垂向短路条 	型号						ITVE.L
	订货号						1SNA 291 349 R1100
屏蔽连接条 	型号	CBD5.2L					
	订货号	1SNA 291 077 R2400					

接线端子 弹簧连接

 - 微型端子  DIN 2  DIN 3		 2个弹簧	 4个弹簧	 2个弹簧	 4个弹簧	 2个弹簧	 4个弹簧	
								
型号		DR 2.5 / 5.2L	DR 2.5 / 10.4L	DS 2.5 / 5.2L	DS 2.5 / 10.4L	DB 2.5 / 5.2L	DB 2.5 / 10.4L	
厚度 (mm)		5	10	5	10	5	10	
最大线径 (mm²)		2.5	2.5	2.5	2.5	2.5	2.5	
标准型 	型号	DR 2.5 / 5.2L	DR 2.5 / 10.4L	DS 2.5 / 5.2L	DS 2.5 / 10.4L	DB 2.5 / 5.2L	DB 2.5 / 10.4L	
	订货号	1SNA 290 201 R1100	1SNA 290 211 R0200	1SNA 290 221 R0400	1SNA 290 231 R0600	1SNA 290 241 R1000	1SNA 290 251 R1200	
零线型 	型号	DR 2.5 / 5.N.2L	DR2.5 / 10.N.4L	DS 2.5 / 5.N.2L	DS 2.5 / 10.N.4L	DB 2.5 / 5.N.2L	DB 2.5 / 10.N.4L	
	订货号	1SNA 290 203 R1300	1SNA 290 213 R0400	1SNA 290 223 R0600	1SNA 290 233 R0000	1SNA 290 243 R1200	1SNA 290 253 R1400	
接地型 	型号	DR 2.5 / 5.PI.2L <small>(不和导轨接触)</small>	DR2.5 / 10.P.4L	DS 2.5 / 5.PI.2L <small>(不和导轨接触)</small>	DS 2.5 / 10.PI.4L <small>(不和导轨接触)</small>	DB 2.5 / 5.PI.2L	DB 2.5 / 10.PI.4L	
	订货号	1SNA 290 210 R1500	1SNA 290 219 R1200	1SNA 290 240 R1100	1SNA 290 240 R2300	1SNA 290 250 R2500	1SNA 290 260 R2700	
终端固定器 	型号	BADRL (DIN 2)		BADL (DIN 3)				
	订货号	1SNA 199 420 R2100		1SNA 399 903 R0200				
端板 	型号	FED1.L						
	订货号	1SNA 291 301 R0200						
端板-凸缘套件 	型号						FEDB.L	
	订货号						1SNA 290 281 R0100	
隔板 	型号	FED2.L						
	订货号	1SNA 291 311 R2300						
短路条  IP20	型号	BJDL5.2 至 BJD5.10	1) BJD10.2 2) BJD10.3 3) BJD10.4 4) BJD10.5	BJDL5.2 至 BJD5.10	1) BJD10.2 2) BJD10.3 3) BJD10.4 4) BJD10.5	BJDL5.2 至 BJD5.10	1) BJD10.2 2) BJD10.3 3) BJD10.4 4) BJD10.5	
	订货号	1SNA 291 102 R2300(2P) 至 1SNA 291 110 R2600(10P)	1)1SNA 291 322 R2600(2P) 2)1SNA 291 323 R2700(3P) 3)1SNA 291 324 R2000(4P) 4)1SNA 291 325 R2100(5P)	1SNA 291 102 R2300(2P) 至 1SNA 291 110 R2600(10P)	1)1SNA 291 322 R2600(2P) 2)1SNA 291 323 R2700(3P) 3)1SNA 291 324 R2000(4P) 4)1SNA 291 325 R2100(5P)	1SNA 291 102 R2300(2P) 至 1SNA 291 110 R2600(10P)	1)1SNA 291 322 R2600(2P) 2)1SNA 291 323 R2700(3P) 3)1SNA 291 324 R2000(4P) 4)1SNA 291 325 R2100(5P)	
标记卡	型号	RC55						
	订货号	请参阅第7/15页						