

















# 接线端子














## ADO 绝缘移位连接

 DIN 2和3							微型ADO		
<b>型号</b>		<b>D1 / 5.ADO</b>	<b>D1.5 / 6.ADO</b>	<b>D1.5 / 6 D2.ADO</b>	<b>D2.5 / 8.ADO</b>	<b>D4 / 8.ADO</b>	<b>DR1.5 / 6.ADO</b>	<b>DR2.5 / 8.ADO</b>	
<b>厚度</b> (mm)		<b>5</b>	<b>6</b>	<b>6</b>	<b>8</b>	<b>8</b>	<b>6</b>	<b>8</b>	
<b>最大线径</b> (mm <sup>2</sup> )		<b>1</b>	<b>1.5</b>	<b>1.5</b>	<b>2.5</b>	<b>4</b>	<b>1.5</b>	<b>2.5</b>	
<b>标准型</b> 	<b>型号</b>	<b>D1 / 5.ADO</b>	<b>D1.5 / 6.ADO</b>	<b>D1.5 / 6.D2.ADO</b>	<b>D 2.5 / 8.ADO</b>	<b>D 4 / 8.ADO</b>	<b>DR1.5 / 6.ADO</b>	<b>DR 2.5 / 8.ADO</b>	
	<b>订货号</b>	1SNA 199 563 R2400	1SNA 199 051 R2600	1SNA 199 480 R2600	1SNA 199 059 R0600	1SNA 399 244 R1400	1SNA 199 283 R2400	1SNA 199 287 R2000	
<b>零线型</b> 	<b>型号</b>	<b>D1 / 5.N.ADO</b>	<b>D1.5 / 6.N.ADO</b>	<b>D1.5 / 6.D2.N.ADO</b>	<b>D2.5 / 8.N.ADO</b>	-	<b>DR1.5 / 6.N.ADO</b>	<b>DR 2.5 / 8.N.ADO</b>	
	<b>订货号</b>	1SNA 199 565 R2600	1SNA 199 053 R2000	1SNA 199 482 R1400	1SNA 199 061 R2000		1SNA 199 285 R2600	1SNA 199 289 R0200	
<b>接地型</b> 	<b>型号</b>	<b>D1 / 5.P.ADO</b>	<b>D1.5 / 6.P.ADO</b>	-	<b>D2.5 / 8.P.ADO</b>	<b>D4 / 8.P.ADO</b>	<b>DR1.5 / 6.PI.ADO</b> (不和导轨接触)	<b>DR 2.5 / 8.P.ADO</b>	
	<b>订货号</b>	1SNA 399 031 R2200	1SNA 199 098 R2600		1SNA 199 091 R1700	1SNA 399 250 R2600	1SNA 199 286 R2700	1SNA 299 633 R0600	
<b>终端固定器</b> 	<b>型号</b>	<b>BADL</b>					<b>BADRL</b>		
	<b>订货号</b>	1SNA 399 903 R0200					1SNA 199 420 R2100		
<b>端板</b> 	<b>型号</b>	<b>FEMAD3</b>		<b>FED2AD2</b>	<b>FEMAD3</b>		<b>FEAD2</b>		
	<b>订货号</b>	1SNA 199 341 R0500		1SNA 199 476 R2500	1SNA 199 341 R0500		1SNA 199 423 R1000		
<b>电流隔板</b> 	<b>型号</b>	<b>SCAD5</b>	<b>SCAD</b>						
	<b>订货号</b>	1SNA 199 551 R2000	1SNA 196 896 R0000						
<b>已装配短路条</b> IP20 10路 	<b>型号</b>	<b>BJMI 5 (10)</b>	<b>BJMI 6 (10)</b>		<b>BJMI 8 (10)</b>				
	<b>订货号</b>	1SNA 176 282 R2300	1SNA 176 667 R0400		1SNA 176 673 R0200				
<b>端子条标识座</b> 	<b>型号</b>	<b>PEAD (放在BADL上, 对端子条进行标识)</b>							
	<b>订货号</b>	1SNA 399 719 R1000							
	<b>型号</b>	<b>EPR2 (放在PEAD的透明保护片, 每张20片)</b>							
	<b>订货号</b>	1SNA 399 726 R0700							
<b>标记卡</b>	<b>型号</b>	<b>RC510</b>	<b>RC610</b>	<b>RC610</b>	<b>RC810</b>	<b>RC810</b>	<b>RC65</b>	<b>RCAL 85</b>	
	<b>订货号</b>	请参阅第7/15页							
<b>A.D.O.专用工具</b>	<b>型号</b>		<b>OUMAD</b>				<b>OUPAD</b>		
	<b>订货号</b>	<b>手动工具</b>	1SNA 179 466 R0600			<b>半自动工具</b>	1SNA 178 944 R0400		

ADO / ADO连接: 端子两侧均为ADO连接

# 接线端子

## ADO 绝缘移位连接 / 螺钉卡箍连接

 <p>ADO / 螺钉卡箍连接 DIN 2和3</p>								<div style="border: 1px solid black; padding: 2px; display: inline-block;">微型ADO</div> 	
型号		D2.5 / 5.ADO	D4 / 6.ADO	D4 / 6D2.ADO	D6 / 8.ADO	D6 / 8.ADO3	DR4 / 6.ADO	DS4 / 6.ADO	
厚度 (mm)		5	6	6	8	8	6	6	
最大线径 (mm <sup>2</sup> )		2.5 (螺钉) 1 (ADO)	4 (螺钉) 1.5 (ADO)	4 (螺钉) 1.5 (ADO)	6 (螺钉) 2.5 (ADO)	6 (螺钉) 4 (ADO)	4 (螺钉) 1.5 (ADO)	4 (螺钉) 1.5 (ADO)	
 <p>标准型</p>	型号	D 2.5 / 5.ADO	D 4 / 6.ADO	D 4 / 6.D2.ADO	D 6 / 8.ADO	D 6 / 8.ADO3	DR 4 / 6.ADO	DS 4 / 6.ADO	
	订货号	1SNA 199 554 R2300	1SNA 199 034 R1500	1SNA 199 242 R0200	1SNA 199 042 R2500	1SNA 199 245 R1500	1SNA 199 275 R0300	1SNA 299 489 R0700	
 <p>零线型</p>	型号	D 2.5 / 5.N.ADO	D 4 / 6.N.ADO	D 4 / 6.D2.N.ADO	D 6 / 8.N.ADO	-	DR 4 / 6.N.ADO	DR 4 / 6.N.ADO	
	订货号	1SNA 199 556 R2500	1SNA 199 036 R1700	1SNA 199 244 R0400	1SNA 199 044 R2700	-	1SNA 199 277 R0500	1SNA 299 491 R2100	
 <p>接地型</p>	型号	D 2.5 / 5.P.ADO	D 4 / 6.P.ADO	-	D 6 / 8.P.ADO	D 6 / 8.P.ADO3	DR 4 / 6.PI.ADO (不和导轨接触)	DS 4 / 6.PI.ADO (不和导轨接触)	
	订货号	1SNA 399 030 R0500	1SNA 199 050 R0100	-	1SNA 199 118 R2600	1SNA 399 251 R1300	1SNA 199 278 R1600	1SNA 299 492 R2200	
 <p>终端固定器</p>	型号	BADL						BADRL	BADRL
	订货号	1SNA 399 903 R0200						1SNA 199 420 R2100	1SNA 399 903 R0200
 <p>端板</p>	型号	FEDAD1		FED2AD1	FEDAD1		FEAD1		
	订货号	1SNA 199 336 R2000		1SNA 199 417 R1200	1SNA 199 336 R2000		1SNA 199 421 R1600		
 <p>电流隔板</p>	型号	SCAD5	SCAD						
	订货号	1SNA 199 551 R2000	1SNA 399 903 R0200						
 <p>已装配短路条</p>	型号	BJMI 5 (10)	BJMI 6 (10)		BJMI 8 (10)			-	
	订货号	1SNA 176 282 R2300	1SNA 176 667 R0400		1SNA 176 673 R0200			-	
 <p>端子条标识座</p>	型号	PEAD (放在BADL上, 对端子条进行标识)						-	
	订货号	1SNA 399 719 R1000						-	
	型号	EPR2 (放在PEAD的透明保护片, 每张20片)						-	
	订货号	1SNA 399 726 R0700						-	
<p>标记卡</p>	型号	RC510	RC610	RC610	RC810	RC810	RC65		
	订货号	请参阅第7/15页							
<p>A.D.O.专用工具</p>	型号	 <p>手动工具</p>	OUMAD			 <p>半自动工具</p>	OUPAD		
	订货号		1SNA 179 466 R0600				1SNA 178 944 R0400		

ADO / 螺钉卡箍连接: 端子一侧为ADO联接, 另一侧为普通的螺钉连接

entelec ADO系列接线端子, 也包括:

- 刀闸型开关接线端子
- 保险丝接线端子